

USB Switched Socket 2G Plate

Stock code: 796-7363



General

Face plate finish:	moulded
Number of outlets:	1/2
Outboard rocker:	No
Rocker finish:	white moulded
Switched:	Yes
With indicator lamp:	No
With RCD:	No

Technical

Associated standards:	EN 60950-1
Base material:	Thermoset
Earth type:	clean
Face plate material:	thermoset
Fixing screws:	2 x M3.5
IP rating:	IP2X
Maximum installation altitude:	2000m
Minimum switch contact gap:	3 mm
Minimum wall box depth:	25
Nature of supply:	AC
Operational testing:	30000
Output voltage:	5V
Rated current:	13A/2A
Rated frequency:	50-60Hz
Rated voltage:	220-250V
Switched poles:	2 pole
Terminal capacity:	3 x 2.5mm 2 x 4.0mm 2 x 6.0mm