



Alphabetical **SEARCH**    Picture **SEARCH**    Part Number **SEARCH**

Go To Step Search™ Screen


**35185** -- *1 of 1 products*

**Terminals and Splices**  
**Ring and Spade Tongue Terminals**

General **INFO**

Sales **INFO**

Customer Drawings **SPECIFICATIONS**



*Line art represents typical product only.*

<b><i>Searchable Features:</i></b>	
<b>Terminal Shape</b>	Ring Tongue
<b>Body Style</b>	SOLISTRAND
<b>Receptacle Style</b>	Straight
<b>Barrel Type</b>	Closed Barrel
<b>Wire/Cable Type</b>	Regular Wire
<b>Wire Range</b>	2 [26.7-42.2] AWG [mm]
<b>Wire Range (CMA)</b>	52,600-83,700
<b>Insulation</b>	No
<b>Insulation Support</b>	Non-Insulation Support
<b>Stud Size</b>	1/2 [M12]
<b>Stud Diameter</b>	.500 [12.70] in. [mm]
<b>Shape</b>	RING-050
<b>Heavy Duty</b>	Standard
<b>Packaging Method</b>	Loose Piece
<b>Material</b>	Copper
<b>Finish</b>	Tin
<b><i>Other Properties:</i></b>	
<b>Dim. C</b>	.531 [13.49] Min. in. [mm]
<b>Dim. E</b>	1.212 [30.79] Max. in. [mm]
<b>Dim. L</b>	1.657 [42.09] Max. in. [mm]
<b>Dim. W</b>	.890 [22.61] in. [mm]
<b>Barrel I.D. Min.</b>	.370 [9.39] in. [mm]
<b>Stock Thickness</b>	.073 [1.85] Max. in. [mm]
<b>CERTI-CRIMP Hand Tool</b>	59975-1
<b>Pneumatic Hand Tool Number</b>	69015-0
<b>Crimping Head for Pneumatic Tool # 69015-0</b>	48174-0
<b>DYNA-CRIMP Tool Number</b>	69120-2
<b>Crimping Head for DYNA-CRIMP Tool # 69120-2</b>	69065-0
<b>Upper Die for DYNA-CRIMP Crimping Head # 69065-0</b>	48130-0
<b>Lower Die for DYNA-CRIMP Crimping Head # 69065-0</b>	48127-0