

Specifications for Bulk BMP71 PermaSleeve Wire Marker Sleeves

Article No.	115011
Brady Material No.	B-342
Material Type	Heat-shrink Polyolefin Sleeve
Colour	White
Finish	Matt
Order Reference	BM71-187-175-342
Printer Compatibility	BMP71
Size - Height (mm)	8.50
Size - Width (mm)	44.83
Additional Information	Heat-shrinkable;Self-Extinguishing
Total Qty per Pack	1000 Sleeve(s) / Box
Wire Gauge	18-12
Approval/Compliance	SAE-AMS-DTL-23053/5 C (Class 1); SAE-AS-81531; MIL-STD-202 method 215K; UL224
Ribbon Series	M71-R4300
Application	Wire & Cable Marking
Industry	Aerospace;Data & Telecommunications;Defence;Electrical;Mass Transit
Description	Bulk roll of PermaSleeve markers. PermaSleeve markers provide a wire marking solution that combines speed, ease of use, and permanence to create long-lasting, high quality identification. These Sleeves are self-extinguishing and meet the requirements of SAE AMS-DTL-23053/5 Class 1, SAE-AS-8153, MIL-STD-202 method 215K and is UL224 recognised. CSA acceptance pending.
Max. Characters per Line	41
Max. Lines of Text	3
Max. Service Temp. °C	130
Max. Wire/Cable Diameter (mm)	3.81

Min. Service Temp. °C	-70
Min. Wire/Cable Diameter (mm)	1.57
Printable Sides	Single-sided Printable
Shape	Rectangle
Shrink Ratio	3:1