



Standard
T&B Catalog Number:

TY300-50

UPC Number:

78621007996

Status:

Active

Description:

Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 302.26mm (11.9 Inches), Width of 4.673mm (0.184 Inches), Thickness of 1.24mm (0.049 Inches), Tensile Strength Rating of 220 Newtons (50 Pounds), Military Specified (MIL-SPEC MS-3367-7), Bulk Pack

Features

The integrally formed nylon pawl combines low insertion and high locking strength.

Standards

UL Listed

General

Material Nylon 6.6
Color Natural

Dimension Information

Nominal Length (inches) 11
Length (inches) 11.4
Width (inches) 0.187
Max. Wire Bundle Diameter (inches) 3
Min. Wire Bundle Diameter (inches) 1/16

Specifications

Temperature Rating -40°F to 185°F
Flammability Rating UL 94 V-2

Tooling

Application Tools ERG50, QC-100, L-200, L-400-C

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com