

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY

FED. MFR. CODE/91929

SWITCH - BASIC

CATALOG LISTING
BA-2RV-A2

ABN7500

BA-2RV-A2

PAGE 1 OF 1

M
DRAWING
NUMBER

ISSUE
810

REPLACES

RELEASE NO.

CHECK

18 JAN 06

RJ


CHECK

5 JAN 02

DAW

CHECK

15 DEC 61



NOTE
▲ - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000 ± .002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE ----- 2 1/2 OZ MAX

RELEASE FORCE ----- 1/2 OZ MIN

PRETRAVEL ----- .625 MAX

DIFFERENTIAL TRAVEL ----- .109 MAX

OVERTRAVEL ----- .078 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

L23

20A - 125, 250 OR 480 VAC
10A - 125 VAC "L"
1HP - 125 VAC, 2HP - 250 VAC
1/2A - 125 VDC, 1/4A - 250 VDC

L288
L308
L315

20(3)A 250V T85 5E4

SCALE --- FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
SPECIFIED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE (.9) ± .030
TWO PLACE (.09) ± .015
THREE PLACE (.009) ± .006
ANGLES ±

WEIGHT

RASTER

0-50378

DRAWN