

Product Information

ETX085x80-Ø20 NL85-Type A

EAN 4031582330908

Wheel centre made of steel, tread made of Polyurethane, casted, precision ball bearing, sealed

Wheel diameter	85 mm
Width of Tread	80 mm
Axle Hole Ø	20 mm
Hub length	85 mm
Temperature	- 20 / + 60 °C
Dynamic Load capacity	800 kg
Static Load capacity	1600 kg
Hardness of tread	A 92 Shore

