

Heavy-duty double headed installation ties


Heavy-duty installation ties

Technical Information


Material	Polyester
Temperature range	-40°C to +80°C
Colour	Black
Flammability rating	UL 94 HB
Other properties	UV-resistant



Single locking head



Double locking head



Product Ref.	Length L [mm]	Width W [mm]	Thickness [mm]	Bundle diameter from ... to [mm]	Minimum tensile strength [N]	Quantity [pieces]	Tooling
CTP-9-180-0-C*	180	9	1.8	10 - 42	440	100	
CTP-9-260-0-C	260	9	2.0	15 - 62	520	100	L300-FR
CTP-9-360-0-C	360	9	2.0	25 - 92	520	100	L-500-EU
CTP-9-500-0-C	510	9	2.4	74 - 140	550	100	WT3D
CTP-9-750-0-C	760	9	2.4	74 - 220	550	100	

* Product Ref. CTP-9-180-0-C has a single locking head

Description of materials and properties: see pages 142 to 153

For tooling specifications: see pages 128 to 141