



## DCF815D2

10.8V XR Li-Ion Impact Driver - 2.0Ah

### Selling Proposition

- Compact body enables operation in confined spaces and repetitive use with minimal fatigue
- Parabolic switch profile allowing for greater control over speed
- All metal gearing for efficient power transmission and long tool life
- 3 LED 'Halo' ring provides maximum illumination to work piece
- 6.35mm 'drop in' keyless hex driver allows for quick, one handed fitment
- Compact, durable design delivers 107Nm of torque

### Standard Equipment

- 2 x 2.0Ah XR Li-Ion battery packs
- Multi-voltage XR charger
- Heavy duty kit box

### Warranty Specifications

- 3 year limited warranty
- 30 Day No Risk Satisfaction Guarantee
- 1 Year Free Service Contract

Specifications	
Battery chemistry	XR Li-Ion
Voltage	10.8 V
Battery Capacity	2.0 Ah
Max Torque	107 Nm
Power Output	147 Watt
No Load Speed	0-2450 rpm
Impacts per Minute	3400 ipm
Max. Bolt Diameter	M10