



ENGLISH

## Datasheet

# Round Fixed Height Feet, PD.2190BL 19mm, PUR, +65°C -34°C

RS Stock number 0248467



### Features

Hemispherical

Flexible polyurethane feet suitable for indoor and limited outdoor applications.

Excellent skid resistance with a high coefficient of friction and excellent resistance to moving and staining

Temperature range -34°C to +65°C

Long ageing resiliency and will not crack or harden

Ideal for use on: glass, aluminium, stainless steel, acrylic plastic, polyethylene, polystyrene, ABS, polypropylene and polycarbonate

To ensure maximum adhesion, surfaces must be clean, dry and well unified