


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION ,19 .
© COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	P	F	REVISIONS				
				ZONE	LTR	DESCRIPTION	DATE	APPD
AF	50				J	REV PER 0G1A-0145-99	3JUN99	JR/JH



- 1 MATES WITH .020±.001 X .110 OR .125 TAB.
- 2 WIRE STRIP LENGTH .281
- 3 INSULATION SIZE .260 MAX DIA
- 4 CONTINUOUS STRIP ON REELS
- 5 DIMENSION DOES NOT INCLUDE TRIM BURR
- 6 .015 MAX CARRIER TRIM BURR PER SIDE IS ALLOWABLE IN THE SHADED AREA

HOUSING: NYLON, COLOR-BLUE TRANSLUCENT RECEPTACLE: #3 HARD BRASS, TIN .000080 MIN		3-520370-2	
MATERIAL & FINISH		PART NO	
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON: 2 PLC DEC ± - 3 PLC DEC ± .015 ANGLES ± - MATERIAL SEE TABLE FINISH SEE TABLE	DR 11/9/88 P FORTNEY	AMP AMP INCORPORATED Harrisburg, Pa. 17105	
	CHK 11/9/88 MS FEHER		
	APPD 11/11/88 K RANDOLPH	NAME RECEPTACLE ASSY, ULTRA-FAST, .110/.125 SERIES, 16-14 AWG	
	APPD 11/11/88 TL SHUTTER		
	PRODUCT SPEC 108-2043	SIZE B	FSCM NO 00779
	APPLICATION SPEC 114-2123	DRAWING NO 520370	
	WEIGHT -	SCALE 4:1	SHEET 1 OF 1