

**BV.FC4 Sealed roller tool chest****Description :**

- High density injected polypropylene resistant to extreme conditions of use. Compatible with military, aerospace... use
- Totally sealed and resists to shock, dust and industrial fluids.
- Several padlock clasps available.
- Stainless steel hinge pins.
- Clasps easy to use.
- Resists pressure differences.
- 2 lateral handles & telescopic handle.
- Temperature tolerance: -33°/+90°.
- Customizable identification plate.
- 4 60mm high drawers + worktop
- Tools accessible from the front or the top.
- Outer dimensions (LxWxD): 581x381x455 mm.

---

**A [mm]:** 581

---

**B [mm]:** 381

---

**C [mm]:** 455

---

**d [mm]:** 59

---

**E [mm]:** 396

---

**[kg]:** 14

---