

Specifications for BMP41/BMP51/BMP53 Labelmaker Labels

Adhesive	Permanent Acrylic
Article No.	131584
Brady Material No.	B-427
Material Type	Self-laminating Vinyl
Colour	Black on White/Transparent
Finish	Matt
Order Reference	M-48-427
Printable Area - Height (mm)	19.05
Printable Area - Width (mm)	9.53
Printer Compatibility	BMP41; BMP51; BMP53
Size - Height (mm)	25.40
Size - Width (mm)	19.05
Additional Information	Self-laminating; Self-extinguishing; Excellent water & oil resistance; Excellent abrasion and smudge resistance
Thickness (mm)	0.102
Total Qty per Pack	200 Label(s) / Box
Vertical Repeat (mm)	22.23
Wire Gauge	12-10
Approval/Compliance	UL Recognised
Adhesive (Y/N)	Yes
Application	Wire & Cable Marking
Max. Service Temp. °C	60
Max. Wire/Cable Diameter (mm)	3.00
Min. Service Temp. °C	-80
Min. Wire/Cable	2.00

Diameter (mm)	
Shape	Rectangle
Software	LabelMark
Surface	For smooth & textured/rough surfaces
Voice/Data Application	CAT 6; 4 pair UTP Copper