


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A1	-		A5	ECR-09-023155	22OCT2009	VG	AR
			A6	ECR-10-009777	17MAY2010	SR	AR

Notes

- 1
- SUITABLE HOUSINGS: SERIES EMV, SIZE 1
CUSTOMER DRAWING 1102700, 1106402, 1106200
- 2
- STANDARDS:
DIN EN 61984, DIN EN 60664-1
- 3
- SUR TEC 650 CHROMIT AL TCP PASSIVATION
- 4
- TOOL:
SLOTTED SCREW DRIVER 4.0x0.8
- 5
- VARNISH ON INSIDE AREA NOT NECESSARY
- 6
- PACKAGING:
10 SETS IN A CARTON, PRE-MOUNTED



PN 0-1 AS SHOWN

1					ANGLED BULKHEAD HOUSING		ALU	BLACK	SERIES EMV-K WITHOUT LOGO	10
	-	x	x	-	GLUE	-	CYANACRYLAT	BLACK	LOCTITE 480	9
	x	-	-	x	GLUE	-	CYANACRYLAT	NATURAL	LOCTITE 401	8
1	1	1	1	1	SCREW, SLOTTED COUNTERS. FLAT HEAD	-	STAINL. STEEL	BLANK	M3x8 DIN EN ISO 2009	7
1	1	1	1	1	HOSE SECTION	-	FKM	BLACK	SERIES EMV / HIP Ø3x1x4.5	6
1	1	1	1	1	PROGFILE SEAL	-	FKM	BLACK	SERIES EMV / HIP	5
	-	1	-	-	ANGLED BULKHEAD HOUSING	M20	ALU	BLACK SEE NOTE 3	SERIES EMV-K	4
	1	-	-	-	ANGLED BULKHEAD HOUSING	M20	ALU	GREY	SERIES EMV-K	3
	-	-	1	-	ANGLED BULKHEAD HOUSING	M16	ALU	BLACK SEE NOTE 3	SERIES EMV-K	2
	-	-	-	1	ANGLED BULKHEAD HOUSING	M16	ALU	GREY	SERIES EMV	1
0-5	0-4	0-3	0-2	0-1		"A"	MATERIAL	COLOR/SURFACE	NOTE	ITEM
PN/QTY					DESCRIPTION					

PARTS LIST (PER ONE UNIT)

0-5	EMV-K.3/4.SG-N
0-4	EMV.3/4.SG.1.M20.G
0-3	EMV-K.3/4.SG.1.M20.G
0-2	EMV-K.3/4.SG.1.M16.G
0-1	EMV.3/4.SG.1.M16.G
PART NO.	ORDERING TEXT

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN V.GLUMM 26AUG2009	Tyco Electronics Tyco Electronics AMP GmbH 64625 Bensheim (Germany)		
DIMENSIONS: mm		CHK H.Braun 26AUG2009			
		APVD T.Schnurpfeil 26AUG2009			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC			
		APPLICATION SPEC	NAME ANGLED BULKHEAD HOUSING ASS'Y SIDE ENTRY, SERIES EMV, SIZE 1		
MATERIAL -		WEIGHT -			
FINISH -		CUSTOMER DRAWING	SIZE A3	CAGE CODE 00779	DRAWING NO C-1106401
			RESTRICTED TO	SCALE 1:1	SHEET 1 OF 1
				REV A6	