

Professionally approved products.

Datasheet

4 Port VGA Splitter

RS Stock number [794-7082](#)



Description:

The NLKVS-range of Video Splitters are designed for desktop use, supplied in a durable, compact metal housing. The splitters duplicate and boost the input signal to 2, 4 or 8 VGA, SVGA or Multi-sync Monitors, with a signal rate of **450 Mhz**. Video Splitters are ideal for applications such as tradeshow, business meetings and demonstrations.

Specification:

- 450Mhz Video Bandwidth
- 4 Port
- Supports up to 2048 x 1536 Resolution
- Supports DDC, DDC2 & DDC2B(Port 1 only)
- Duplicate one signal input to multiple outputs
- Ability to be cascaded
- Effective transmission distance: 65 Mtrs
- Power saving mode
- Metal Case

Contents

- Video Splitter
- Power Supply
- User Manual