


AMP

WIRE RANGE

8 AWG

STRANDED



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 105°c		-	LOOSE PC		53041		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: - -	DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 0.20 [.008] 3 PLC DEC ± - ANGLES ± -	DR 6-18-93 S.S. GOULDEN	PACKAGE TYPE			PART NO
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 6.64-10.5mm² [13,100-20,800] STRANDED	MATERIAL COPPER PER ASTM B-152 NYLON (MIL-M-20693) TYPE 1 COLOR: RED	CHK 6-18-93 R. HERSEY	AMP Incorporated Harrisburg, PA 17105-3608			
FOR ORDER ENTRY		1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		FINISH TIN PLATE PER MIL-T-10727	APPD 6-18-93 B. BARE	NAME			
						APPD 6-18-93 M. ELLIS	TERMINAL, RING TONGUE, TERMINYL WIRE SIZE: 8 AWG			
						PRODUCT SPEC -	SIZE	CAGE CODE	DRAWING NO	
						APPLICATION SPEC -	B	00779	C=53041	
						WEIGHT -	SCALE	NTS	SHEET	1 OF 1