



Main

Range	Multi 9
Product or component type	OC contact
Device short name	OFS
Signal contacts composition	1 C/O
[In] rated current	3 A at 380...415 V AC - 50/60 Hz 6 A at 220...240 V AC - 50/60 Hz 1 A at 130 V DC 1.5 A at 60 V DC 2 A at 48 V DC 6 A at 24 V DC
9 mm pitches	1

Complementary

Range compatibility	Multi 9 GFP GFP Multi 9 C60 C60BP Multi 9 C60 C60BPR Multi 9 C60 C60SP Multi 9 C60H-DC C60H-DC
Mounting mode	Fixed
Mounting support	DIN rail
Height	84 mm
Width	9 mm
Depth	73 mm
Connections - terminals	Clamp terminal 2 cable(s) 1.5 mm ² flexible Clamp terminal 2 cable(s) 1.5 mm ² rigid Clamp terminal 1 cable(s) 0.5...2.5 mm ² rigid Clamp terminal 1 cable(s) 0.5...2.5 mm ² flexible
Wire stripping length	9 mm
Tightening torque	1 N.m

Environment

Standards	EN/IEC 60947-5-1
Product certifications	CEBEC DEMKO FIMKO NEMKO

SEMKO

IP degree of protection	IP20 conforming to EN/IEC 60947-5-1
Pollution degree	3 conforming to EN/IEC 60947-5-1
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-25...50 °C
Ambient air temperature for storage	-40...85 °C

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0716 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------