



Sample photo

Order symbol: ALN 316018
Product nbr: 7811480
Description: Enclosure
Remarks: Aluminium

EAN: 6418074016263
El. number:
Finland:
:

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		600	310	180	Ingress Protection (EN 60529): IP 66/67/68
inch:		23.6	12.2	7.1	Impact Resistance (EN 62262): IK 08
Materials:					NEMA Class: NEMA 1, 4, 4X, 12, 13
Material:	Aluminium				Certificates: Underwriters Laboratories Fimko Gost R
Base colour:	RAL 7001				
Cover colour:	RAL 7001				
Cover screws material:	Stainless steel				
Gasket material:	Polyurethane				
Temperatures:					
Short term:	-50 ... 140 °C				
Continuous:	-50 ... 80 °C				
Short term:	-60 ... 285 °F				
Continuous:	-60 ... 175 °F				
Accessories:					
AM 3160	Mounting plate				
ARH 60	DIN-35 Mounting rail				
MRS 28541	Wall fastening lug (2 pcs)				
PH A & AH A/B	Hinge set				

