



Sample photo

Order symbol: AB 081209
Product nbr: 7083600
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074058775
EI. number:
 Finland: 3435466
 Electric No. 8212003321
 Denmark:
 Electric No. Sweden: 7083600

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:				Rating:
	Length	Width	Height	
mm:	120	80	85	Ingress Protection (EN 60529): IP66/IP67
inch:	4.7	3.1	3.3	Impact Resistance (EN 62262): IK07
Materials:				Electrical insulation: Totally insulated
Material:	ABS			Halogen free (DIN/VDE 0472, Part 815): 1
Base colour:	RAL 7035 -light grey			Flammability Rating: UL 94 HB
Cover screws material:	Stainless steel			Glow Wire Test (IEC 695-2-1) °C: 650
Cover colour:	RAL 7035 -light grey			NEMA Class: NEMA 1, 4, 4X, 12, 13
Gasket material:	Polyurethane			
Temperatures:				
Temperature °C (short term):	-40 ... 80 °C			
Temperature °C (continuous):	-40 ... 60 °C			
Temperature °F (short term):	-40 ... 175 °F			
Temperature °F (continuous):	-40 ... 140 °F			

