



ENGLISH

Datasheet

Socket Sets

## 46 PC 1/4" Ratchet, Bit & Socket Set



[RS Stock no. 623-6441](#)

### Material

Chrome vanadium (50 BV 30) steel for socket and accessories, carbon steel ratchet bit driver shaft & P.P/TPR double injection grip and chrome molybdenum (s-2) steel for bits and P.P/TPR double injection grip



**Finish**

Satin chrome plated with knurled upon central portion for sockets, chrome plated bit driver shaft, sandblast finish for bits double injection grip

**Hardness**

Heat treated to HRC: 38 ~ 54 (Sockets), HRC: 56 ~ 62 (bits)

**Contents**

1 pc-1/4" hexagonal reversible ratchet bit driver double injection grip & end cap storage (magnetic shaft, minimum torque test load - 15.0 newton - m)

12 pcs-1/4" dr. Sallow socket: (6pt) Imperial: 3/16", 1/4", 5/16", 11/32", 3/8", 7/16", Metric: 6, 7, 8, 10, 11, 13 mm

1 pc-1/4" hexagonal to 1/4" dr. Socket adapter (25 mm)

32 pc-1/4" (6.35 mm) hexagon screw driver bits, 4 holders: (length - 25 mm)  
Sl: 3, 4, 4.5, 5, 5.5, 6, 7 & 8 mm Ph: no.0, 1, 2 & 3 Pozi: no.0, 1, 2 & 3 Hex bits: 1.5, 2, 2.5, 3, 4, 5, 5.5 & 6 mm tamper proof torx: t-8, t-10, t-15, T-20, t-25, t-27, t-30 and t-40

Each set in blow mould case

**Remark**

Socket, bit and ratchet bit driver meet requirement of din standard