

Special configurations

Cable operated flange

30A - 800A



Lug Kit



OZX-200

Terminal lug kits

| For use with | Wire size | Wire type | Description | Lugs per kit | Catalog number |
|-----------------|--------------------------------|----------------|-----------------------|--------------|-----------------------|
| OS100GJ30 | #4 - 300 kcmil | Cu/Al | - | 6 | OZX-24 |
| OS200J30 | #4 - 300 kcmil (6) #4-6 AWG | Cu/Al Cu/Al | - Distribution lug | 3 3 | OZX-200/3 OZX-206S |
| OES400 | #2 - 600 kcmil | Cu/Al | - | 6 | OZX-26 |
| | #2 - 600 kcmil | Cu/Al | - | 3 | OZX-26/3P |
| | (2) #2 - 500 kcmil | Cu/Al | Distribution lug | 6 | OZX-33 |
| OES600 - OES800 | (12) #14 - 6 kcmil | Cu/Al | - | 3 | OZX-175/400 |
| | (2) #2 - 600 kcmil | Cu/Al | - | 6 | OZX-27 |
| | (2) #2 - 600 kcmil | Cu/Al | Distribution lug | 3 | OZX-27/3P |

Door hardware NEMA 12

| Item | Catalog number |
|--|----------------|
| Safety door latch, 2 point, door less than 40" high | KDH2R |
| Safety door latch, 3 point, door greater than 40" high | KDH3R |

Terminal shrouds

| For use on | Description | Weight (lbs.) | Catalog number |
|------------|---|---------------|----------------|
| OS100 | 1 Pole | 0.04 | OSS160T1 |
| OS100 | 3 Pole | 0.12 | OSS160T3 |
| OS200 | 3 Pole Long Type Shroud | 0.2 | OSS200G1L/3 |
| OS200 | 3 Pole Short Type Shroud | 0.13 | OSS200G1S/3 |
| OES400 | 3 Pole (includes one shroud for line and load side) | 0.13 | OESA-ZX123 |
| OES600 | 3 Pole (includes one shroud for line and load side) | 0.13 | OESA-ZX125 |
| OES800 | 3 Pole (includes one shroud for line and load side) | 0.11 | OESA-ZX125 |