

RoHS Compliant

US-279

USB2Serial 8xRS232

"SERIAL CARDS ENGINEERED TO EXCEED EXPECTATIONS"



Description

USB to Serial providing 8 RS232 serial ports. Up to 921,600 data transfer rates and the 128 byte deep transmit and 384 byte receive FIFOs, coupled with 1Mbit line drivers deliver uncompromising performance on your laptop/PC.

USB to serial is the quick low cost way to connect your computer to a serial comms enabled device. Boost software gives industry leading functionality and compatibility.

These products do away with traditional issues with USB technology so you can buy with confidence!

With Brainboxes industry renowned Lifetime Warranty and Lifetime Support!

Features

- 8 port RS232
- USB to Serial
- 128 Byte Tx and 384 Byte Rx FIFOs
- Up to 921,600 Baud
- 8xDB9 connector (9 Pin Male) Industrial high retention USB connector
- Drivers for all popular operating systems
- Sample Programs, Test & Terminal software
- Lifetime Support
- Lifetime Warranty (registration required)

Options



US-279:
USB2Serial 8xRS232



Software

Microsoft signed drivers (easy installation & robust operation) for:

- Windows Vista 32 bit and 64 bit editions
- Windows XP 32 bit & 64 bit editions

64Bit
Driver

As well as: full product documentation, a thorough troubleshooting guide and terminal software. Detailed sample source code for many popular programming languages. Further OS support on next page.



Microsoft
GOLD CERTIFIED
Partner

ORDER

Description
USB2Serial 8xRS232

Code
US-279

US-279: Full Specification

32 bit & 64 bit Editions
2 bit & 64 bit Editions

IC: CE Microsoft Certified Gold Part
fied Gold Partner

including manual, Microsoft signed
S232

registration required)

Email and Phone Support from fully
in and alongside the Product Deve

bulk buy OEM