

## Electronic housing - UM122-SEFE/L - 2908773

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Side element, left, with foot, width: 5 mm, length: 122 mm, for mounting on DIN rail NS 32 or NS 35/7.5



The illustration shows the article with further components

### Why buy this product

- Flexible size and shape
- Wide range of options for external conductor connection
- Inexpensive as a result of reducing the number of separate housing parts
- High degree of mechanical stability by screwing the lateral elements to the profile
- Can be snapped onto standard NS 35/7,5 and NS 35/15 DIN rails

### Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 017918 160692
Weight per Piece (excluding packing)	8.32 g
Custom tariff number	39269097
Country of origin	Poland

### Technical data

#### General

Housing type	Panel mounting base
Color	green

### Classifications

#### eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 6.0	27180802

# Electronic housing - UM122-SEFE/L - 2908773

## Classifications

### eCl@ss

eCl@ss 7.0	27182701
eCl@ss 8.0	27182701

### ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC000721

### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

## Approvals

### Approvals

---

Approvals

UL Recognized

---

Ex Approvals

---

Approvals submitted

---

### Approval details

UL Recognized 
---