



## Symphoni IP AV

VERSATILE RANGE OF UK &  
EUROPEAN TONES  
ULTRA LOW POWER  
CONSUMPTION  
INTEGRATED LED BEACON  
PROTECTION TO IP66  
COMPACT DESIGN BASED  
ON THE SYMPHONI

Model	Symphoni IP AV
Nominal Voltage	
Current Consumption (tone dependant)	
Sound Output (tone dependant)	100db(A)
Alarm Tones	5
IP Rating	IP66
Lens Colour	Clear
Flash Rate	1Hz
Beacon Type	LED
Voltage Rating	18 to 30Vdc
Current	10mA max
Volume Control	10dB, by switch
Light Output	>1Cd
Synchronisation	20ms over 30m
Flash Colour	Red
Monitoring	Diode (reverse polarity)
Temperature Range	-25 degrees C to +70 degrees C
Base Lock	

- > Power Supplies
- > Relays
- > Remote Indicators
- > Powered Base

**Security Products**

- > Mosquito Ultrasonic
- > Firecat
- > Security Cage

**French Approved Products**

- > French Askari Standard Class A
- > French RoLP Standard Class B
- > French Symphoni Range

**UL & FM Approved Products**

- > Bells
- > Horn/Strobes
- > Speaker/Speaker Strobe
- > DSM Sync Module
- > Mounting Accessories

Copyright © Fullleon Limited | [Privacy & Legal](#)