



ENGLISH

Datasheet

RS Pro PUR 10m Long transparent Flexible Ducting Reinforced, 45mm Bend Radius, Applications Various

RS Stock No: **399-0827**



Product Details

RS Pro 10 m long reinforced transparent flexible ducting features polyurethane (PU) hosing with a copper plated steel spiral for durability. The ducting has 45 mm bend radius and is suitable for suction and the transport of dusts, chips and abrasive materials. The hose offers excellent internal and external abrasion resistance. It is also suitable for oil and petrol fume extraction.

Features and Benefits

- Copper coated spring steel spiral helix between 2 layers of crystal clear flexible polyurethane
- Excellent internal and external abrasion resistance
- Retains full diameter even in tight bending radii
- Suitable for the transfer of large abrasive particles such as sawdust, timber off cuts and metal swarf
- Also suitable for oil and petrol fume extraction
- Temperature range from -40 to +90°C



ENGLISH

Specifications:

Bend Radius	45 mm
Colour	Transparent
Inner Diameter	45 mm
Length	10 m
Material	PUR
Outer Diameter	50
Reinforced	Yes
Suitable Applications	Abrasive Material, Chemical, Dust, Granule, Saw Dust, Oil & Petrol Fume Extraction
Wall Thickness	0.7 mm
Operating Temperature	-25 to +125°C