

4
DRAWING MADE IN THIRD ANGLE PROJECTION

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION, 19

© COPYRIGHT 19

BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC
G

DIST
14

P

F

ZONE

LTR

REVISIONS

DESCRIPTION

DATE

APPD

AMP
PART NO

MATERIAL

PKG
TYPE

QTY

8-36916-3

M/F 8-36916-0


BOX

25

REVISED PER 0720-0465-95

03MAR95

OKS RER



AMP WIRE RANGE	E13288 Listed
1/0 AWG SOLID OR STRANDED	1/0 AWG SOLID OR STRANDED
LR7189 Certified	MILITARY P/N AND CLASS
1/0 AWG SOLID OR STRANDED	NOT APPLICABLE

- 1 STAMP AMP 1/OW* APPROX AS SHOWN
2 MATERIAL THK: 1.78±0.08 [.070±.003]

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

MAX RECOMMENDED OPERATING
TEMPERATURE:
170°C MAX

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm [INCHES]
TOLERANCES ON:
2 PLC DEC ± 0.20 [0.008]
3 PLC DEC ± -
ANGLES ± -

DR 7/2/91
DK SCHRUM
CHK 8/15/91
RD HEIM
APPD 8/15/91
AJ KAUFMAN
APPD 8/15/91
AJ ADELMANN
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

AMP AMP Incorporated
Harrisburg, PA 17105-3608

NAME
TERMINAL, RING TONGUE,
SOLISTRAND™

SIZE
B

CAGE CODE
00779

DRAWING NO
C-36916

SCALE
2:1

SHEET
1 OF 1

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

VOLTAGE RATING:
NOT APPLICABLE

WIRE CROSS SECTIONAL AREA RANGE:
42.4-60.6mm² [83,700-119,500] CIR MILS
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

36916

PART NO