

# Product Information

## PJP125x32-Ø8

EAN 4031582070262

Wheel centre made of Polypropylene, Tread: TENTEprene (thermoplastic rubber), grey non-marking, precision ball bearing, with threadguards

Wheel diameter	125 mm
Width of Tread	32 mm
Axle Hole Ø	8 mm
Hub length	36.5 mm
Temperature	- 20 / + 60 °C
Standard	EN 12530
Weight	0.276 kg
Dynamic Load capacity	100 kg
Static Load capacity	200 kg
Hardness of tread	A 87 Shore



### Versions:

