

PATCHCABLE DUPLEX 4XT-ST 62,5



Specifications

Communication Channels	Duplex
Connector A	ST
Connector B	ST
Core Diameter	62.5/125 μ m
Fibre Type	OM1
Length	2m
Propagation Mode	Multi Mode
Sheath Colour	Orange

ST Patch Cable

Cores designed for easier splicing with compact construction and loose secondary coating to enable very fast, easy splicing

Technical specifications	
Type	Cable
Core construction:	Tight buffer
Core Ø:	0.9 mm
Cable design:	Kevlar strain relief
Outer sheath:	PVC, orange
External Ø:	Type 2.8 mm
Operating temperature:	-20 °C → +80 °C
Storage temperature:	-40 °C → +90 °C
Standard length:	2 m