






- CONTINUOUS STRIP ON REELS.
- ACCEPTS WIRE SIZE [#16-#12 OR TWO #16'S].
- INSULATION RANGE TO BE 4.06-5.33 [.160-.210] OR TWO 3.30 [.130] MAX DIA.
- MATING TAB THK IS 0.81 ± 0.025 [.032 ± 0.001].
- INTERLEAVING PAPER REQUIRED.
- PRELIMINARY - NOT FOR PRODUCTION



5	0.002032 [.000080] MIN TIN	6	60249-5
	0.000381 [.000015] THK SILVER		60249-3
	TIN		60249-2
	-		60249-1
	FINISH		PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL
H04 BRASS

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± 0.38 [.015]
3 PLC ± -
4 PLC ± -
ANGLES ± -

FINISH
SEE TABLE

DWN
JR RUTH
7/14/95

CHK
MS FEHER
7/14/95

APVD
J GILLESPIE
7/14/95

PRODUCT SPEC
-

APPLICATION SPEC
114-2025

WEIGHT
-

TE Connectivity

NAME
RECEPTACLE, FASTIN-FASTON,
6.35 [.250] SERIES

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-60249

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
5:1

SHEET
1 of 1

REV
F