



view of the hood without lid

Cable diameter  $\varnothing 8 - 12$   
Cable diameter  $\varnothing 8 - 12$

5	2	Locking screw	FV51/5-K1163 4-40 / Steel	nickel plated
4	1	Cable clamp	Steel	fin plated
3	4	Screw	Case hardened steel	zinc plated
2	2	Catch spring	Polyester	black
1	1	Hood	FMK5-2940 / Zinc die-cast	nickel plated
No.	St.	Part	Type Description / Material	Surface plating / Colour / Class

		SCALE	TITLE
		ISO 2768-m	2.1
		NAME / DATE	Anke Meyer-Richter
		DATE	07-11-2011
		CHECKED	BWittrek
		CHECKED	07-11-2011
		ORIGINAL: DIN A3-DRAWING AS A FILE	
REV.	DATE	CH.-NO.	REPLACEMENT FOR:
1			
			DWG.NO. FMK5-4881
			REV. 1
			PAGES 1

Packing unit on supplement AM0409

max. torque are 40 Ncm

The cable outlet is suitable for two cables 16x2x0.5

COMMENT:  
ALL RIGHTS ARE RESERVED BY US FOR THIS DRAWING. WITHOUT OUR PRIOR CONSENT,  
IT MAY NOT BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS,  
ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEM.  
AND IT ALSO MAY NOT BE IMPROPERLY USED BY THE RECEIVER, OR A THIRD PARTY.