


PCB Headers
1513960000



SL 5.08/90, Single row, 90° Orientation,
Open End, Non-locking



Representative Photo

Technical Information

Connector Options	Pin Header
Pitch	5.08 mm
Poles	15
Orientation	90°
Type	Open End
Locking	No
Color	Orange
Rated Voltage UL	300 V
Rated Current UL	15 A
Configuration	Single row

Technical Data

	UL	CSA	VDE
Rated Voltage	300 V	300 V	250 V
Rated Current	15 A	15 A	12 A

Additional Data

Connector End Type	Open
Mating Parts	BL 5.08 BLC 5.08 BLDT 5.08 BLIDC 5.08 BLL 5.08 BLT 5.08 BLZ 5.08 BLZF 5.08

Insulation material	PBT
Temperature Range	-20°C...+100°C (-4°F...+212°F)
Flammability Class	UL 94 (V-0)
Contact Base Material	CuSn
Contact Plating	Tin-Plated
Solder Pin Length	4.5 mm
PCB Hole Diameter	1.3 ^{+0.1} mm
Insulation Resistance	> 10 ⁵ M Ohms
Through Resistance	< 4.5 m Ohms
VDE 0110 1.89 Rated Current	12/8 A
Rated Voltage - III/3	250 V
Impulse Voltage - III/3	4.0 kV
Rated Voltage - III/2	400 V
Impulse Voltage - III/2	4.0 kV
Rated Voltage - II/2	400 V
Impulse Voltage - II/2	4.0 kV

Suggested Accessories

Coding Element

Dividing Block

KSW marking strips

Light Guides

Product Liability The above information describes our products. It does not constitute guaranteed properties and is not intended to affirm the suitability of a product for a particular application. Regrettably, omissions and exceptions cannot be completely ruled out. Technical data are always specified by their average values. Exact data and the tolerances which apply to our processes can be requested from:

Weidmüller - North America
United States 001 (800) 849-9343
Canada 001 (800) 268-4080

or

Weidmüller - Germany
Telephone operator 0049 (-5252) 960-0