



ENGLISH

Datasheet

RS Pro Xenon V10994 Series Light Bar, Amber, Flashing, Surface Mount, 10 → 30 V dc

RS Stock No: **235-376**



Product Details

RS Pro xenon flashing light bar is available as 7 W or high power 21 W version. This single or double flash xenon light bar has amber coloured lens that is suitable for commercial, fleet or utility vehicles. It offers IP56 degree of protection and reverse polarity protection. It measures 188 x 550 x 230 mm. The light bar supports single point surface mounting.

Features and Benefits

- Dual voltage (12/24 V)
- Single or double flash xenon light bar
- IP56 protection
- Reverse polarity protection
- Flash rate: 125 fpm
- Single point mounting
- Measures 188 x 550 x 230 mm



ENGLISH

Specifications:

Bulb Type	Xenon
Current Type	DC
Housing Colour	Black
Lamp Included	Yes
Lens Colour	Amber
Light Effect	Flashing
Special Features	Reverse Polarity Protection
Standards Met	ECE 65; RoHS Compliant
Base Length	550 mm
Base Width	230 mm
Height	188 mm
Maximum Temperature	+50°C
Minimum Temperature	-30°C
IP Rating	IP56
Mounting Style	Surface Mount
Supply Voltage	10 to 30 V dc
Flash Rate	125 fp/min