



Beschreibung:

- > Spritzwassergeschützte Headlight mit 5 LED´s
- > Für einen optimierten Tragekomfort ist die Energieversorgung vom Leuchtkörper der Headlight abgekoppelt und an der Rückseite des Tragebandes angebracht
- > Die Lichtintensität beträgt 300 Lux bei einer Leuchtweite von ca. 100 m
- > Der Neigungswinkel der Headlight kann individuell eingestellt werden
- > Die Leuchtdauer beträgt bis zu 20 Stunden



Description:

- > The High quality ANSMANN HD5 water proof headlight includes five-piece LED.
- >This product is supplied with 3x ANSMANN AAA batteries. The battery pack is situated at the back of the head, held in place with two-strap headband for extra comfort.
- >The angle of the Headlight can be personalised by the user.
- >The headlight's operating time is up to 20 hours.
- >This product is supplied with a 3 year warranty.

INFOS | INFORMATION:

Produktname | Product name:
HEADLIGHT HD5

Art.-Nr. | Part No.:
5819083

EAN-Code:
4013674190836

Verpackungseinheit | Packing Unit:
4 (210x155x270mm)

Exportkarton | Export Carton:
24 (490x235x560mm)

Lieferbar | Available:
Ab Lager | In stock

Zolltarifnummer | Customs tariff number:
85131000

Lieferumfang | Included in delivery:
> 3x Micro AAA Alkaline Batterien | Batteries

Notizen / Notes:



Headlight HD5