

G83-6104/G83-6105



Models may vary from the image shown

Proven millions of times over!

There's a reason why this keyboard has been one of the most reliable and successful on the market for many years, with more than 30 million satisfied users.

Key benefits

- NTK technology (elastomer keys with membrane contact switches)
- Space-saving, compact design
- Long-lived and recycling-friendly
- Comfortable actuation
- Uniform switching characteristics
- Abrasion-proof inscription of key caps

Technical Data:

Layout (country or language):

Product dependant, see table "Models"

Housing colour:

Product dependant, see table "Models"

Key colour:

Product dependant, see table "Models"

Weight (product):

662 g

Total weight (with packaging):

810 g

Cable Length:

approx. 1.75 m

Storage Temperature:

-20°C to 60°C

Operating Temperature:

0°C to 50°C

Current Consumption:

typ. 16 mA

Interface:

Product dependant, see table "Models"

Product approvals:

- cURus
- VDE GS
- c-tick
- CE
- FCC



System requirements:

Product dependant, see table "Models"

Delivery Volume:

- G83-6104/G83-6105
- Printed instructions

Dimensions (product):

approx. 458 x 170 x 42 mm

Packaging dimensions:

approx. 493 x 210 x 47 mm

Keyboard:

- Key technology: NTK
- Service life, standard key: > 20 million key operations
- Operation characteristics: Soft pressure point
- Inscription technology: Laser
- Inscription layout: Standard
- Number of Keys: Product dependant, see table "Models"

Packaging Unit:

- Number of products in the master package: 65
- Number of master packages per pallet: 2

Warranty:

2 years

Errors, technical changes and delivery possibilities excepted.
Technical information refers only to the specifications of the products. Features may differ from the information provided.

Models:

(possible country/layout versions, others available on request)

	Product name	Order number	EAN code	Layout (country or language)	Housing colour	Key colour	Interface	System requirements	Number of Keys
1	G83-6104	G83-6104LPNAR-0	4025112024863	English (US) / Arabic	light grey	light grey	PS/2	PS/2 connection	104
2	G83-6104	G83-6104LPNAR-2	4025112041754	English (US) / Arabic	black	black	PS/2	PS/2 connection	104
3	G83-6104	G83-6104LPNEU-2	4025112011887	US English with EURO symbol	black	black	PS/2	PS/2 connection	104
4	G83-6104	G83-6104LPNIL-0	4025112012174	English (US) / Hebrew	light grey	light grey	PS/2	PS/2 connection	104
5	G83-6104	G83-6104LPNJK-0	4025112054990	Japan (Katakana)	light grey	light grey	PS/2	PS/2 connection	104
6	G83-6104	G83-6104LPNRC-0	4025112055003	English (US) / Chinese	light grey	light grey	PS/2	PS/2 connection	104
7	G83-6104	G83-6104LRNEU-0	4025112010248	US English with EURO symbol	light grey	light grey	PS/2	PS/2 connection	104
8	G83-6104	G83-6104LRNRB-0	4025112044168	English (US) / Cyrillic	light grey	light grey	PS/2	PS/2 connection	104
9	G83-6104	G83-6104LUNAR-2	4025112056598	English (US) / Arabic	black	black	USB	USB connection	104
10	G83-6104	G83-6104LUNEU-0	4025112010880	US English with EURO symbol	light grey	light grey	USB	USB connection	104
11	G83-6104	G83-6104LUNEU-2	4025112028793	US English with EURO symbol	black	black	USB	USB connection	104
12	G83-6104	G83-6104LUNIL-0	4025112056550	English (US) / Hebrew	light grey	light grey	USB	USB connection	104
13	G83-6104	G83-6104LUNRC-0	4025112049927	English (US) / Chinese	light grey	light grey	USB	USB connection	104
14	G83-6104	G83-6104LUNRG-0	4025112006876	US / Cyrillic	light grey	light grey	USB	USB connection	104
15	G83-6104	G83-6104LUNRG-2	4025112057915	US / Cyrillic	black	black	USB	USB connection	104
16	G83-6105	G83-6105LPNBE-0	4025112010262	Belgium	light grey	light grey	PS/2	PS/2 connection	105
17	G83-6105	G83-6105LPNEE-0	4025112044281	Estonia	light grey	light grey	PS/2	PS/2 connection	105
18	G83-6105	G83-6105LPNES-0	4025112010286	Spain	light grey	light grey	PS/2	PS/2 connection	105

	Product name	Order number	EAN code	Layout (country or language)	Housing colour	Key colour	Interface	System requirements	Number of Keys
19	G83-6105	G83-6105LPNES-2	4025112015236	Spain	black	black	PS/2	PS/2 connection	105
20	G83-6105	G83-6105LPNGB-0	4025112010699	UK	light grey	light grey	PS/2	PS/2 connection	105
21	G83-6105	G83-6105LPNGB-2	4025112034466	UK	black	black	PS/2	PS/2 connection	105
22	G83-6105	G83-6105LPNHU-0	4025112045646	Hungary	light grey	light grey	PS/2	PS/2 connection	105
23	G83-6105	G83-6105LPNNL-0	4025112010675	Netherlands	light grey	light grey	PS/2	PS/2 connection	105
24	G83-6105	G83-6105LPNNL-2	4025112050596	Netherlands	black	black	PS/2	PS/2 connection	105
25	G83-6105	G83-6105LPNNO-0	4025112040665	Norway	light grey	light grey	PS/2	PS/2 connection	105
26	G83-6105	G83-6105LPNNO-2	4025112027390	Norway	black	black	PS/2	PS/2 connection	105
27	G83-6105	G83-6105LPNPO-0	4025112010668	Portugal	light grey	light grey	PS/2	PS/2 connection	105
28	G83-6105	G83-6105LPNRD-0	4025112021220	Germany / Cyrillic	light grey	light grey	PS/2	PS/2 connection	105
29	G83-6105	G83-6105LPNSF-2	4025112048524	Sweden / Finland	black	black	PS/2	PS/2 connection	105
30	G83-6105	G83-6105LRNBE-2	4025112017278	Belgium	black	black	PS/2	PS/2 connection	105
31	G83-6105	G83-6105LRNCH-0	4025112010644	Switzerland	light grey	light grey	PS/2	PS/2 connection	105
32	G83-6105	G83-6105LRNCH-2	4025112036965	Switzerland	black	black	PS/2	PS/2 connection	105
33	G83-6105	G83-6105LRNDE-2	4025112000034	Germany	black	black	PS/2	PS/2 connection	105
34	G83-6105	G83-6105LRNDK-0	4025112045837	Denmark	light grey	light grey	PS/2	PS/2 connection	105
35	G83-6105	G83-6105LRNDK-2	4025112047541	Denmark	black	black	PS/2	PS/2 connection	105
36	G83-6105	G83-6105LRNEE-2	4025112003080	Estonia	black	black	PS/2	PS/2 connection	105
37	G83-6105	G83-6105LRNFA-0	4025112053818	French / Arabic	light grey	light grey	PS/2	PS/2 connection	105
38	G83-6105	G83-6105LRNFR-0	4025112010309	France	light grey	light grey	PS/2	PS/2 connection	105
39	G83-6105	G83-6105LRNFR-2	4025112013638	France	black	black	PS/2	PS/2 connection	105
40	G83-6105	G83-6105LRNGR-0	4025112046476	Greece	light grey	light grey	PS/2	PS/2 connection	105
41	G83-6105	G83-6105LRNHU-2	4025112003134	Hungary	black	black	PS/2	PS/2 connection	105
42	G83-6105	G83-6105LRNIT-0	4025112057441	Italy	light grey	light grey	PS/2	PS/2 connection	105
43	G83-6105	G83-6105LRNIT-2	4025112011405	Italy	black	black	PS/2	PS/2 connection	105
44	G83-6105	G83-6105LRNPL-0	4025112053825	Poland	light grey	light grey	PS/2	PS/2 connection	105
45	G83-6105	G83-6105LRNPL-2	4025112003318	Poland	black	black	PS/2	PS/2 connection	105
46	G83-6105	G83-6105LRNPO-2	4025112001178	Portugal	black	black	PS/2	PS/2 connection	105
47	G83-6105	G83-6105LRNRD-2	4025112049088	Germany / Cyrillic	black	black	PS/2	PS/2 connection	105
48	G83-6105	G83-6105LRNSF-0	4025112029516	Sweden / Finland	light grey	light grey	PS/2	PS/2 connection	105
49	G83-6105	G83-6105LRNSK-2	4025112003264	Slovakia	black	black	PS/2	PS/2 connection	105
50	G83-6105	G83-6105LRNSL-0	4025112010316	Slovenia	light grey	light grey	PS/2	PS/2 connection	105

	Product name	Order number	EAN code	Layout (country or language)	Housing colour	Key colour	Interface	System requirements	Number of Keys
51	G83-6105	G83-6105LRNSL-2	4025112011733	Slovenia	black	black	PS/2	PS/2 connection	105
52	G83-6105	G83-6105LRNTS-0	4025112023682	Czech Republic	light grey	light grey	PS/2	PS/2 connection	105
53	G83-6105	G83-6105LRNTS-2	4025112003219	Czech Republic	black	black	PS/2	PS/2 connection	105
54	G83-6105	G83-6105LRPDE-0	4025112010002	Germany	light grey	light grey	PS/2	PS/2 connection	105
55	G83-6105	G83-6105LUNBE-0	4025112010637	Belgium	light grey	light grey	USB	USB connection	105
56	G83-6105	G83-6105LUNBE-2	4025112043178	Belgium	black	black	USB	USB connection	105
57	G83-6105	G83-6105LUNCH-0	4025112017308	Switzerland	light grey	light grey	USB	USB connection	105
58	G83-6105	G83-6105LUNCH-2	4025112047350	Switzerland	black	black	USB	USB connection	105
59	G83-6105	G83-6105LUNDE-0	4025112010330	Germany	light grey	light grey	USB	USB connection	105
60	G83-6105	G83-6105LUNDE-2	4025112026027	Germany	black	black	USB	USB connection	105
61	G83-6105	G83-6105LUNDK-0	4025112010620	Denmark	light grey	light grey	USB	USB connection	105
62	G83-6105	G83-6105LUNDK-2	4025112047329	Denmark	black	black	USB	USB connection	105
63	G83-6105	G83-6105LUNES-0	4025112010613	Spain	light grey	light grey	USB	USB connection	105
64	G83-6105	G83-6105LUNES-2	4025112046216	Spain	black	black	USB	USB connection	105
65	G83-6105	G83-6105LUNFR-0	4025112010347	France	light grey	light grey	USB	USB connection	105
66	G83-6105	G83-6105LUNFR-2	4025112028779	France	black	black	USB	USB connection	105
67	G83-6105	G83-6105LUNGB-0	4025112010606	UK	light grey	light grey	USB	USB connection	105
68	G83-6105	G83-6105LUNGB-2	4025112047336	UK	black	black	USB	USB connection	105
69	G83-6105	G83-6105LUNGR-0	4025112056765	Greece	light grey	light grey	USB	USB connection	105
70	G83-6105	G83-6105LUNIT-0	4025112010590	Italy	light grey	light grey	USB	USB connection	105
71	G83-6105	G83-6105LUNIT-2	4025112046209	Italy	black	black	USB	USB connection	105
72	G83-6105	G83-6105LUNNL-0	4025112044717	Netherlands	light grey	light grey	USB	USB connection	105
73	G83-6105	G83-6105LUNNL-2	4025112050510	Netherlands	black	black	USB	USB connection	105
74	G83-6105	G83-6105LUNNO-0	4025112013249	Norway	light grey	light grey	USB	USB connection	105
75	G83-6105	G83-6105LUNNO-2	4025112042843	Norway	black	black	USB	USB connection	105
76	G83-6105	G83-6105LUNPL-0	4025112052781	Poland	light grey	light grey	USB	USB connection	105
77	G83-6105	G83-6105LUNPO-0	4025112047398	Portugal	light grey	light grey	USB	USB connection	105
78	G83-6105	G83-6105LUNPO-2	4025112047343	Portugal	black	black	USB	USB connection	105
79	G83-6105	G83-6105LUNRD-0	4025112041990	Germany / Cyrillic	light grey	light grey	USB	USB connection	105
80	G83-6105	G83-6105LUNRD-2	4025112054082	Germany / Cyrillic	black	black	USB	USB connection	105
81	G83-6105	G83-6105LUNSF-0	4025112047381	Sweden / Finland	light grey	light grey	USB	USB connection	105
82	G83-6105	G83-6105LUNSF-2	4025112042621	Sweden / Finland	black	black	USB	USB connection	105

	Product name	Order number	EAN code	Layout (country or language)	Housing colour	Key colour	Interface	System requirements	Number of Keys
83	G83-6105	G83-6105LUNSL-0	4025112010583	Slovenia	light grey	light grey	USB	USB connection	105
84	G83-6105	G83-6105LUNTS-0	4025112022364	Czech Republic	light grey	light grey	USB	USB connection	105
85	G83-6105	G83-6105LUNTS-2	4025112040351	Czech Republic	black	black	USB	USB connection	105