

Fuse - SI FORM C 10 A DIN 72581 - 0913715

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Flat-type plug-in fuse, type C, color code: red, nominal current: 10 A




The figure shows a version of the article

Why buy this product

- Fuse holder for flat-type fuses with a maximum nominal voltage of 32 V
- With snap-in foot for secure pre-assembly on the PCB

Key commercial data

Packing unit	50 pc
GTIN	 4 017918 008673
Weight per Piece (excluding packing)	1.85 g
Custom tariff number	85361010
Country of origin	Germany

Technical data

General

Color	red
Inflammability class according to UL 94	V0

Dimensions

Width	5 mm
Length	19 mm
Height NS 35/7,5	13 mm

General

Fuse	C
Nominal current I_N	10 A
Nominal voltage U_N	24 V

Fuse - SI FORM C 10 A DIN 72581 - 0913715

Classifications

eCl@ss

eCl@ss 4.0	27141199
eCl@ss 4.1	27141199
eCl@ss 5.0	27142007
eCl@ss 5.1	27142007
eCl@ss 6.0	27142001
eCl@ss 7.0	27142008
eCl@ss 8.0	27142008

ETIM

ETIM 2.0	EC000899
ETIM 3.0	EC002298
ETIM 4.0	EC002298
ETIM 5.0	EC002298

UNSPSC

UNSPSC 6.01	30211813
UNSPSC 7.0901	39121410
UNSPSC 11	39121412
UNSPSC 12.01	39121412
UNSPSC 13.2	39121412

Approvals

Approvals

Approvals

GOST

Ex Approvals

Approvals submitted

Approval details

GOST
