

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

, -.

© COPYRIGHT 2011APR BY-Tyco Electronics Japan G.K.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

C

REVISED

25APR11




MM

NY

NOTES


1 MATERIAL:HOUSING:GLASS FILED THERMO PLASTIC
,POLYESTER(94V-0),
COLOR:1- /2- : BLACK
: 9- : NATURAL

2 TO COAT ALL SURFACE OF HOUSING WITH TEFLON



2.5XN=A

KEY LOCATION VIEW
2-1318119-4
(KEYING Y)



LOGO MARK

SERIES MARK

OBSOLETE		11.4	10.8	7.5	3	8	5-1318119-4
	—	11.4	10.8	7.5	3	8	2-1318119-4
	—	11.4	10.8	7.5	3	8	1-1318119-4
OBSOLETE		8.9	8.3	5	2	6	5-1318119-3
	—	8.9	8.3	5	2	6	9-1318119-3 2-1318119-3
	—	8.9	8.3	5	2	6	1-1318119-3
FINISH	C	B	A	N	POS	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN K.IKEDA 7/DEC/'98	TE Connectivity				
DIMENSIONS: mm		CHK N.MATSUBARA 7/DEC/'98					
		APVD I.HASEGAWA 7/DEC/'98					
TOLERANCES UNLESS OTHERWISE SPECIFIED		PRODUCT SPEC					
10: ±0.3 30: >10 : ±0.35 100: >30 : ±0.4 ANGLE : ±3°		108-5619	DOUBLE ROW REC HSG <DYNAMIC D-2100D>				
MATERIAL		APPLICATION SPEC					
FINISH		114-5258	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
		WEIGHT	A3	00779	©-1318119	—	
CUSTOMER DRAWING					SCALE	SHEET	REV
					4-1	1 OF 1	C