

## Snap-in markers - UCT-EM (20X7) - 0801494

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Snap-in markers, Sheet, white, unlabeled, can be labeled with: THERMOMARK CARD, BLUEMARK CLED, BLUEMARK LED, TOPMARK LASER, Mounting type: snapped into marker carrier, Lettering field: 20 x 7 mm



### Key commercial data

|                                      |                                                                                                         |
|--------------------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit                         | 10 pc                                                                                                   |
| Minimum order quantity               | 10 pc                                                                                                   |
| GTIN                                 | <br>4 046356 673426 |
| Weight per Piece (excluding packing) | 10.24 g                                                                                                 |
| Custom tariff number                 | 39269097                                                                                                |
| Country of origin                    | Germany                                                                                                 |

### Technical data

#### Dimensions

|            |       |
|------------|-------|
| Length (b) | 20 mm |
| Width (a)  | 7 mm  |

#### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 120 °C |
|---------------------------------|-------------------|

#### General

|                                         |                                |
|-----------------------------------------|--------------------------------|
| Color                                   | white                          |
| Components                              | free from silicone and halogen |
| Inflammability class according to UL 94 | V0                             |
| Material                                | PC                             |
| Wipe resistance                         | DIN EN 61010-1 (VDE 0411-1)    |
| Number of individual labels             | 24                             |
| Number of individual labels per row     | 6                              |
| RoHS compliant                          | Yes                            |
| Printability                            | Thermal transfer               |
|                                         | Inkjet printing                |

## Snap-in markers - UCT-EM (20X7) - 0801494

### Technical data

#### General

|                                                                     |                                    |
|---------------------------------------------------------------------|------------------------------------|
| Device                                                              | 5146464 THERMOMARK CARD            |
|                                                                     | 0801735 THERMOMARK CARD-UCT-MAG8   |
|                                                                     | 5147888 BLUEMARK LED               |
|                                                                     | 5147999 BLUEMARK CLED              |
| Ink ribbon                                                          | 0801371 THERMOMARK-RIBBON 110-TC   |
|                                                                     | 5147421 BLUEMARK FLUID-CARTRIDGE   |
|                                                                     | 5146662 BLUEMARK CLED-FLUID-CARTR. |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02               |
| Result                                                              | Test passed                        |
| Test specification weathering-resistance                            | Following ISO 4892-2:2013-03       |
| Test duration                                                       | 96 h                               |
| Wipe resistance test result                                         | Test passed                        |
| Salt spray test specification                                       | DIN EN 60068-2-11:2000-02          |
| Test duration                                                       | 96 h                               |
| Salt spray testing result                                           | Test passed                        |
| Alternating condensation climate with SO2 test specification        | DIN 50018:2013-05                  |
| Climate level                                                       | AHT 1.0 S                          |
| Cycles                                                              | 2                                  |
| Condensation test result                                            | Test passed                        |
| Wipe resistance of test specification inscriptions                  | IEC 61010-1:2010-06                |
| Result                                                              | Test passed                        |
| Marking mounting type                                               | snapped into marker carrier        |

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 24190219 |
| eCl@ss 4.1 | 24190219 |
| eCl@ss 5.0 | 27141137 |
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |
| eCl@ss 8.0 | 27141137 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC000761 |

#### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 6.01 | 30211811 |
|-------------|----------|

## Snap-in markers - UCT-EM (20X7) - 0801494

### Classifications

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121410 |
| UNSPSC 12.01  | 39121410 |
| UNSPSC 13.2   | 39121410 |

### Accessories

#### Accessories

#### Magazine

Magazine - THERMOMARK CARD-UCT-MAG8 - 0801735



Magazine for the THERMOMARK CARD printer, for accommodating UCT sheets UCT-EM (10 x 7), UCT-EM (15 x 10), UCT-EM (17.5 x 8)

---

### Drawings

#### Pictogram

