

# LED LENSER® i6ER

The LED Lenser i6ER torch is one of the first pen lights available with a re-charging option and is perfect for penetrating less accessible locations that need plenty of light. Its longer barrel is ideal for illuminating narrow or confined spaces in workshops, factories and garages. The precise patented Advanced Focus System reflector lens optics and CREE® Power LED Light Chip are optimised to deliver a stunning eight hour run time when being used at the lights 60 lumen output or up to 25 hours on its low light glare-free setting of 10 lumens. Integrated Speed Focus enables the light to shine bright, homogenous white light all the way from flood to spot beam, and is capable of picking out a component or blemish some distance away with pinpoint accuracy. An easy-grip metal body make handling comfortable for extended use. Recharging is easy via the supplied docking station with no need for removal of the batteries from the actual torch. This simple contact charging ensure the torch is ready to be used instantly when needed.

As a leading international brand of hand-held torches and head lamps, LED Lenser is renowned for superior German engineering, outstanding performance, and state-of-the art technologies, such as the patented Advanced Focus System and Smart Light Technology. Constantly driving innovation to provide class- leading lighting instruments, LED Lenser is the brand of choice for professional tradesmen, emergency services personnel, search & rescue teams and serious outdoor enthusiasts. LED Lenser hand torches and head lamps deliver breath-taking, bright homogenous white light, that turns night into day and simply has to be seen to be believed. Using only the finest materials, such as energy-efficient CREE LED light chips, aircraft-grade aluminium and gold-plated contacts, they are renowned for quality and have a reputation for reliability that is second to none.

- Rechargeable pen-light torch with contact charging docking station
- CREE® Power LED Light Chip
- State-of-the-art, reliable German engineering
- Advanced Focus System (AFS). Patented reflector and lens combination for intense spot (distance ) or flawless flood (near ) illumination
- Speed Focus® (one-handed spot-to-flood beam)
- Dynamic Switch
- Power and Low Power light modes
- Docking station with charging indicator
- USB connection
- Clip
- Water-resistant (IPX4)
- Robust metal housing
- Supplied with: USB Cable , Charging Docking Station, Pouch, Rechargeable Battery Set (3 x AAA NiMH)

<b>Technical Information</b>	Power	Low Power
Lumens	60	10
Beam Distance (meters)	80	30
Run Time (hours)	8	25
Size:	170x18.5mm Ø	
Weight:	82g	
Batteries:	3 x AAA NiMH	

<b>Code</b>	<b>Description</b>	<b>Unit Colour</b>	<b>Packaging</b>	<b>Barcode</b>
5606ER	i6ER	Black	Box	4029113560665
<b>RRP ex.vat £33.29 / incl.vat £39.95</b>				

\* Also compatible with AAA Alkaline batteries (not supplied)