

Datasheet

RS Pro 160mA Radial Non-Resettable Wire Ended Fuse, 250 V

RS Stock No: **767-5086**



Product Details

RS Pro radial non-resettable fuse withstands currents up to 160 mA and voltages up to 250 V. It has thermoplastic body for added durability. This fast acting fuse forms a convenient and reliable solution to a vast array of application requirements.

Features and Benefits

- Fast acting fuse
- Non-resettable
- Radial fuse
- Wire-ended

Specifications:

Body Height	7.7 mm
Body Length	8.35 mm
Body Material	Thermoplastic
Body Width	4.3 mm
Breaking Capacity (at Maximum Voltage Rating)	35 A at 250 V ac
Current Rating	160 mA
Lead Orientation	Radial
Maximum Operating Temperature	+125°C
Minimum Operating Temperature	-55°C
Voltage Rating	250 V
Voltage Rating	250 V
Wire Diameter	0.62 mm
Wire Length	22 mm, 4.3 mm
Wire Pitch	5.08 mm
Fuse Type	Fast Acting
Nominal Resistance	0.829 Ω
Standards Met	VDE, CSA, UL, CCC, RoHS