



- 3-piece styles available
- Precision honed bore on straight bore couplings
- Does not mar the shaft
- Nypatch® Anti-vibration hardware
- Additional Step Bores available
- Bore tolerance:  
+.051mm  
- .000mm
- Opposing hardware on 2-piece styles

PART NUMBER STEEL	PART NUMBER ALUMINUM	PART NUMBER STAINLESS STEEL	BORE B1 (mm)	BORE B2 (mm)	OD (mm)	LENGTH L (mm)	FORGED CLAMP SCREW
MCLX-6-6-F	MCLX-6-6-A	MCLX-6-6-SS	6	6	18	30	M3X8
MCLX-8-7-F	MCLX-8-7-A	MCLX-8-7-SS	8	7	24	35	M3X10
MCLX-8-8-F	MCLX-8-8-A	MCLX-8-8-SS	8	8	24	35	M3X10
MCLX-9-9-F	MCLX-9-9-A	MCLX-9-9-SS	9	9	24	35	M3X10
MCLX-10-9-F	MCLX-10-9-A	MCLX-10-9-SS	10	9	29	45	M4X12
MCLX-10-10-F	MCLX-10-10-A	MCLX-10-10-SS	10	10	29	45	M4X12
MCLX-12-9-F	MCLX-12-9-A	MCLX-12-9-SS	12	9	29	45	M4X12
MCLX-12-12-F	MCLX-12-12-A	MCLX-12-12-SS	12	12	29	45	M4X12
MCLX-14-12-F		MCLX-14-12-SS	14	12	34	50	M5X16
MCLX-14-14-F		MCLX-14-14-SS	14	14	34	50	M5X16
MCLX-15-14-F		MCLX-15-14-SS	15	14	34	50	M5X16
MCLX-15-15-F		MCLX-15-15-SS	15	15	34	50	M5X16
MCLX-16-16-F		MCLX-16-16-SS	16	16	34	50	M5X16
MCLX-20-19-F		MCLX-20-19-SS	20	19	42	65	M6X16
MCLX-20-20-F		MCLX-20-20-SS	20	20	42	65	M6X16
MCLX-25-24-F		MCLX-25-24-SS	25	24	45	75	M6X16
MCLX-25-25-F		MCLX-25-25-SS	25	25	45	75	M6X16
MCLX-30-28-F		MCLX-30-28-SS	30	28	53	83	M6X18
MCLX-30-30-F		MCLX-30-30-SS	30	30	53	83	M6X18
MCLX-35-35-F		MCLX-35-35-SS	35	35	67	95	M8X25
MCLX-40-40-F		MCLX-40-40-SS	40	40	77	108	M8X25
MCLX-50-50-F		MCLX-50-50-SS	50	50	85	124	M10X25

**Ruland Manufacturing Company, Inc.**  
6 Hayes Memorial Drive  
Marlborough, MA 01752  
Phone: 508-485-1000 Fax: 508-485-9000  
Phone: 800-225-4234 Fax: 800-929-9205  
email: [sales@ruland.com](mailto:sales@ruland.com)