



List Price \$521.00 USD

Availability **Stock Item:** This item is normally stocked in our distribution facility.**Technical Characteristics**

Frame Type	F-Frame
Circuit Breaker Type	Standard Interrupting
For Use With	Industrial Enclosures and Switchboards
AC Magnetic Trip Setting	1450A Fixed Trip (800A Hold)
Ampere Rating	60A
Approvals	UL Listed - CSA Certified
Marketing Trade Name	Square D
HACR Rated	Yes
Voltage Rating	480VAC
Mounting Type	Unit Mount
Weight	5 Pounds
Number of Poles	3-Pole
Short Circuit Current Rating	18000AIR@480VAC
Type	FA
Wire Size	(1)#12 to #1/0 AWG(Al) or (1)#14 to #1/0 AWG(Cu)
Width	4.50 Inches
Depth	4.16 Inches
Height	6.00 Inches

Shipping and Ordering

Category	00902 - Circuit Breakers, Thermal Magnetic, 480Vac, Type FAL, UL, Unit Mount
Discount Schedule	DE2
Article Number	785901423386
Package Quantity	1
Weight	4.62 lbs.
Availability Code	S
Returnability	Y

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.