

Datasheet

RS Pro Right Angle 50Ω PCB Mount BNC Connector, jack, Solder Termination Nickel

RS Stock No: **546-5137**



Product Details

RS Pro right angle PCB mount BNC connector features metal housing with a bayonet coupling, nickel plated body and gold plated centre contact. This female connector has 50 Ω impedance. It is suitable for a variety of applications including video signalling and test equipment.

Features and Benefits

- Metal housing with a bayonet coupling, nickel plated body and gold plated centre contact
- Solder termination method
- Female connector
- Suitable for a variety of applications including video signalling and test equipment

**Specifications:**

Body Orientation	Right Angle
Body Plating	Nickel
Contact Material	Phosphor Bronze
Contact Plating	Gold
Gender	Female
Impedance	50 Ω
Mounting Type	PCB Mount
Operating Frequency	0 to 1 GHz
Polarity	Normal
Termination Method	Solder
Insulation Resistance	5000 M Ω
Operating Temperature Range	-40 to +60°C
Standards Met	RoHS Compliant