

Specifications for BMP51/53 Labelmaker Labels

Adhesive	Repositionable Rubber
Application	Laboratory Identification
Approval/Compliance	UL Recognised
Article No.	131591
Brady Material No.	B-498
Material Type	Vinyl Cloth
Brand	CleanLift™ Series
Colour	Black on White
Environment	Freezer
Finish	Semi-gloss
Laboratory Application	Bottles, Flasks & Dishes; General Identification
Max. Service Temp. °C	80
Order Reference	M-128-498
Printer Compatibility	BMP41; BMP51; BMP53
Shape	Rectangle
Size - Height (mm)	48.26
Size - Width (mm)	25.40
Additional Information	Repositionable
Total Qty per Pack	100 Label(s) / Box
Industry	Healthcare; Laboratory
Min. Service Temp. °C	-40
QTY. per Row	1
Thickness (mm)	0.185