



1 TABLE-1

CONTACT CODE	APPLICABLE WIRE	RATED VOLTAGE
PX50-SC-31 (*印→1 LOOSE PIECE) (*印→2 STRIP)	AWG#16 AWG#18	10A 8A

NOTES 1 APPLICABLE CONTACT, APPLICABLE WIRE AND RATED VOLTAGE IS SHOWN IN TABLE 1.
 SPECIFIED CURRENTS ARE RATED VALUE PER CONTACT.
 (40A PER 4 CONTACTS FOR AWG#16 WIRE)
 2 .NOT FOR INTERRUPTING CURRENT.
 3 .ORDER TO BE MADE PER 100PCS.

TO	Q1		
----	----	--	--

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
2	RE-E-06362	N.M	S.M	99.6.21					
4	RE-E-06478	N.M	S.H	99.8.24					

NO.	MATERIAL	FINISH, REMARKS	NO.	PBT	MATERIAL	FINISH, REMARKS
1	CL		1		(BLACK) UL94V-0	

CODE NO. (OLD)	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
	M.Kenjo	M.Kenjo	S.Matsuzaki	A.Nakazawa	

DRAWING NO.	PART NO.
EDC3-121448	PX50-AD4S

SCALE	UNITS	CODE NO.
2 : 1	mm	CL236-0006-3