

Datasheet

RS 20 Core Unscreened Industrial Cable, PVC Sheath, 8.1mm OD, 0.22 mm² CSA 1 A, 440 V, 25m

RS Stock number 660-4061



Electrical Characteristics

Max.Conductor DC Resistance at 20°C (Ω /Km) :
<92

Min.Insulation DC Resistance at 20°C (M Ω *KM) :
>200

Current Rating : 1 A

Marking(3times/m):

RS 6604061 7 - 2 - 20A



Description:

Rated Temperature (°C): -20 ~ 80

Rated Voltage (V):440

Flammability Test: IEC60332-1

Standard:

Manufacture to Def. Stan 61.12 Part 4 & 5

Construction:

Conductor:Tinned Copper

Conductor Dia. (mm): 0.20±0.008 x 7

Insulation: PVC

Insulation Dia. (mm): 1.2±0.05 x 20C

Tape: Mylar Spiral

Coverage: ≥115%

ID Thread: Green, White/Green

A rip cord : 210 D

Jacket: FR-PVC

Outer Dia. (mm): 7.8±0.2

Colour:

The color of the insulation: Red , Blue , Green ,
Yellow , White , Black , Brown , Violet , Orange , Pink , Light
Green , Grey , Red/Blue , Green/Red , Yellow/Red ,
White/Red , Red/Black, Red/Brown, Yellow/Blue , White/Blue

The jacket color: Black

