

DUSTING TOOLS V-3000

V-3000

Mini Vacuum



EAN: 9 00330862200 5

DUSTING TOOLS

extend our range of GREEN-CLEAN aerosols AIR + VACUUM POWER into multifunctional tools. Extremely robust and designed for repeated use on many cans. The improved method is time-saving due to better working advantages, at the same time preventing the use of unnecessary one way part.

The particles removed are collected in a transparent, washable plastic container. Permanent high grade steel filters prevent the fine particles from escaping during the vacuuming process. This mini vacuum cleaner can be applied in those cases where dusting is not possible.

The high pressure of Air + Vacuum Power results in a suction strength similar to that of a 2 m high water column – even the smallest particles can be lifted from inaccessible component parts.

Anwendungsvorteile MINI VACUUM

- Components not exposed to expansion pressure
- No direct contact with gas
- No whirling or extrusion of particles
- Optional: PICK UP protective tube abrasion-free material (DSLR cameras)

To use with GREEN CLEAN AIR POWER:

G-2016	150 ml / 173 gr	not flammable
G-2041	400 ml / 342 gr	flammable
G-2051	400 ml / 462 gr	not flammable



Technical Details:

Description		Size in cm	Weight	Private Logo	Material:
Mini Vac		Schlauchinnendurchmesser 2mm / steel 0,1 x 0,1 x 0,063 mm	44,6 gr.	no	Schlauch: PU Kessel: PC Edelstahlgewebe stainless
Packaging	Units				
Box	4 Units	21,0 x 8,0 x 20,5	282,9 gr.	Shipping	Storage
Box	12 Units	27,0 x 21,5 x 20,7	729,6 gr.	No reg.	No reg.
Pallet / Rows	15 x 12 Units =	180 Units	10,94 kg	Tariff Number	Chem. Reg.
max. Rows :	6 Rows =	1080 Units	65,66 kg	8428995	No reg.

DUSTING TOOLS V-3000

V-3000

Mini Vacuum



EAN: 9 00330862200 5

DUSTING TOOLS erweitern GREEN CLEAN AirDuster zum multifunktionalen Werkzeug zum Ausblasen oder Absaugen, mit Anti Static Wirkung oder mit Verlängerungen

Unterdruck Prinzip zum schonenden Absaugen oder Abheben von Kleinstteilchen

Anwendungsvorteile MINI VACUUM

- kein direkter Gaskontakt
- kein Verpressen und Verwirbeln von Staubteilchen
- waschbarer Auffangbehälter



Zu verwenden mit GREEN CLEAN AIR POWER:

G-2016	150 ml / 173 gr	unbrennbar
G-2041	400 ml / 342 gr	brennbar
G-2051	400 ml / 462 gr	unbrennbar



Technische Beschreibung:

Beschreibung		Maße in cm	Gewicht	Private Logo	Material:
Mini Vac Ventil mit Venturi Rohr		Schlauchinnendurchmesser 2mm / steel 0,1 x 0,1 x 0,063 mm	44,6 gr.	nein	Schlauch: PU Kessel: PC Edelstahlgewebe stainless
Verpackung	Stück				
Kreuzhülle	4 Stk.	21,0 x 8,0 x 20,5	282,9 gr.	Versand	Lagerung
Karton	12 Stk.	27,0 x 21,5 x 20,7	729,6 gr.	keine Vo	keine Vo
Palette je Reihe	15 x 12 Stk = 180 Stk.		10,94 kg	ZollPosnr.	ChemVo
max. Reihen :	6 Reihen = 1080 Stk.		65,66 kg	8428995	keine Vo