

NOTES:

1. HOUSING: GLASS FILLED THERMOPLASTIC UL 94 V-0 RATED; GREY

2. CONTACTS: COPPER ALLOY

3. PLATING:


CONTACT AREA: PERFORMANCE LEVEL 1 OR 2 (SEE TABLE)



ACCORDING TO DIN 41612 AND EN 60603-2, TYPE G

SOLDERING AREA: 3-7µm TIN OVER 0,8µm NICKEL

CONNECTOR IS PRINTED WITH PARTNUMBER AND DATECODE

PART IDENTICAL TO 5-9

	P/N	PERF.LVL	CONTACT ASSIGNMENT																								POS
			1								2								3								
	4-2	1	1	2	3	4	5	6	7	8	9	0	1	2	3	4	5	6	7	8	9	0	1	2			
	5-9	2	z	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	64		
	6-0	2	d	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+			
			f	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+			
			1								2								3								
			1	2	3	4	5	6	7	8	9	0	1	2	3	4	5	6	7	8	9	0	1	2			
			z	v	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+			
			b	v	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	v	64		
			d	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+			
			f	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+	+			
			+ CONTACT																								
			v PREMATING CONTACT 1,3mm																								



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH -

MATERIAL

-

DWN J.van Hoek 050CT2007

CHK B.Mooij 160CT2007

APVD J.Broeksteeg 160CT2005

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

CUSTOMER DRAWING

Tyco Electronics Corporation
's-Hertogenbosch, Nederland

NAME
EUROCARD MALE CONNECTOR TYPE G
64 POS. ANGLED

SIZE A3

CAGE CODE 00779

DRAWING NO C-4-1393755-2

RESTRICTED TO -

SCALE 1:1

SHEET 1 OF 1

REV A1