

## General Information

Extended Product Type:	216MPR6W
Product ID:	2CMA168058R1000
EAN:	7392696680585
Catalog Description:	Switched interlocked socket-outlet with RCD, 6h, 30mA, 16A, IP67, 2P+E
Long Description:	Switched Interlocked Socket Outlet with RCD, earthing sleeve position 6h, 30mA, rated current 16A, IP67 watertight, 2-poles+earth, frequency 50-60 Hz, color code Blue

## Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Switched Interlocked Socket Outlets with RCD

## Ordering

EAN:	7392696680585
Minimum Order Quantity:	1 piece
Country of Origin:	Czech Republic (CZ)

## Dimensions

Product Net Width:	130 mm
Product Net Height:	375 mm
Product Net Length:	182 mm
Product Net Weight:	1.7 kg

## Container Information

Package Level 1 Width:	143 mm
Package Level 1 Length:	397 mm
Package Level 1 Height:	187 mm
Package Level 1 Gross Weight:	1.7 kg
Package Level 1 EAN:	7392696680585
Package Level 1 Units:	1 piece

## Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2007 Q1
--------------	---------------------------------------------------------------------------------------

## Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	2CMC700044D0001
Environmental Information:	2CMC700001D0002
RoHS Information:	2CMC700057D0001

## Additional Information

Additional Information:	Cable entry, knock-outs 2xØ25mm
Cable Cross-Section:	1.5 ... 4 mm <sup>2</sup>
Cable Entry Position:	Top
Cable Outlets Per Side:	2xØ25
Color:	Blue
Degree of Protection:	IP67
Enclosure Material:	Thermoplastic
Frequency (f):	50 Hz 60 Hz
Function:	Switched interlocked socket outlet with RCD, 30 mA
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	Ind. P&S#216MPR6W
Number of Poles:	3
Number of RCD 30mA:	1
Number of RCDs:	1
Object Classification Code:	2CMT005069
Product Main Type:	MPR
Product Name:	Industrial Switched Interlocked Socket Outlet
Protection Type:	Watertight
Rated Current (I <sub>n</sub> ):	16 A
Rated Residual Current:	30mA

<b>Rated Voltage (U<sub>r</sub>):</b>	200 ... 250 V
<b>RoHS Date:</b>	L23
<b>Standards:</b>	IEC 60 309-1, -2, -4
<b>Suitable For:</b>	Switched Interlocked Socket Outlets with RCD
<b>Suitable for Product Class:</b>	Industrial Plugs and Sockets

---

### Classifications

---

<b>E-number:</b>	2466201
<b>UNSPSC:</b>	39120000

---

