




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 11-4-86 L A MAYER		 TE Connectivity					
		CHK 11-12-86 P de Jong							
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME RCPT ASSY, AMPMODU MTE, SINGLE ROW, .100 C/L, LATCHED & POLARIZED FOR #22-#25 AWG WIRE SIZE, STRIP FORM					
		APVD 11-12-86 P de Jong							
		PRODUCT SPEC 108-25034							
		APPLICATION SPEC 114-25026							
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
HOUSING:		SEE TABLE		A2	00779	C-103957	—		
CUSTOMER DRAWING				SCALE	4:1	SHEET	1 of 2	REV	N2

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		—	SEE SHEET 1	—	—	—

13 OBSOLETE	12	2	2.40	1.198	1-104257-1	12	6-103957-1	
	12	2	2.20	1.098	1-104257-0	1 1	6-103957-0	
	12	2	2.00	.998	104257-9	10	5-103957-9	
	12	2	1.80	.898	104257-8	9	5-103957-8	
	12	2	1.60	.798	104257-7	8	5-103957-7	
	12	2	1.40	.698	104257-6	7	5-103957-6	
	12	4	2.39	.598	104257-5	6	5-103957-5	
	12	4	1.99	.498	104257-4	5	5-103957-4	
	12	5	1.99	.398	104257-3	4	5-103957-3	
	12	8	2.40	.298	104257-2	3	5-103957-2	
	12	10	2.00	.198	104257-1	2	5-103957-1	
	11 11	10	2	1.40	.698	104257-6	7	2-103957-0
		10	2	2.40	1.198	1-104257-1	12	1-103957-9
		10	2	2.00	.998	104257-9	10	1-103957-8
		10	2	1.60	.798	104257-7	8	1-103957-7
		10	4	2.39	.598	104257-5	6	1-103957-6
		10	4	1.99	.498	104257-4	5	1-103957-5
		10	5	1.99	.398	104257-3	4	1-103957-4
		10	8	2.40	.298	104257-2	3	1-103957-3
		10	10	2.00	.198	104257-1	2	1-103957-2
		9	2	2.40	1.198	1-104257-1	12	1-103957-1
	9	2	2.20	1.098	1-104257-0	1 1	1-103957-0	
	9	2	2.00	.998	104257-9	10	103957-9	
	9	2	1.80	.898	104257-8	9	103957-8	
	9	2	1.60	.798	104257-7	8	103957-7	
	9	2	1.40	.698	104257-6	7	103957-6	
	9	4	2.39	.598	104257-5	6	103957-5	
	9	4	1.99	.498	104257-4	5	103957-4	
	9	5	1.99	.398	104257-3	4	103957-3	
	9	8	2.40	.298	104257-2	3	103957-2	
	9	10	2.00	.198	104257-1	2	103957-1	
	PLATING		6	B	A	HOUSING PART NUMBER	NO OF POSN	ASSEMBLY PART NUMBER ON STRIP

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± .02
3 PLC ± .005
4 PLC ± -
ANGLES ± -
FINISH
SEE TABLE

DWN
L A MAYER
CHK
P de Jong
APVD
P de Jong

11-4-86
11-12-86
11-12-86

PRODUCT SPEC
108-25034
APPLICATION SPEC
114-25026
WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

RCPT ASSY, AMPMODU MTE, SINGLE ROW, .100 C/L, LATCHED & POLARIZED FOR #22-#25 AWG WIRE SIZE, STRIP FORM

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-103957

RESTRICTED TO
-

SCALE
1:1

SHEET
2 of 2

REV
N2