




REV	DESCRIPTION	DATE
-----	-------------	------

NOTE:

1. MAXIMUM ELECTRIC CURRENT:
A.W.G. 16 14
AMP. 10 15
2. MAXIMUM ELECTRICAL RATING:
125°C 300 VOLTS MAX.
3. INSULATION MATERIAL: PC
4. INSULATION COLOR: RED
5. TERMINAL MATERIAL: COPPER
6. WIRE RANGE: 22-16 A.W.G. (0.5-1.5mm²)
7. TERMINAL THICKNESS: 0.35mm

Tolerance Unless Otherwise Specified	
0 > mm ±	ANGLE
> mm ±	0° REF ±
> mm ±	° ±
> mm ±	° ±

NAME	PC-INSULATED FEMALE DISCONNECTORS				UNIT	mm	
PART NO.	FDM1-187(5)	MATERIAL			APPROVE		
NUMBER	TNV-470	SCALE	SHEET	PAGE	CHECKED		
DATE	09/07/2005	4 : 1	1-0	1 OF 1	DRAWN		