



1475K8



TOOL TROLLEYS

- 8 drawer trolley
- Lock & Go latching system prevents drawers opening when moving the trolley
- Long ball bearing slides with 100% opening drawers
- Scratch resistant paint
- Available in different colours
- Big capacity heavy duty construction trolley
- Double wall frame protects the slides and drawers from shocks/crashes
- Reinforced areas to reduce stress in specific points of the trolley
- Strong and secure round type key and central locking mechanism
- Wheels of 125 x 50 mm with ball bearings and non-marking rubber surface
 - 2 fixed
 - 2 swivel with brake
- Drawers internal dimensions:
 - (8 x) 543 x 445 x 63 mm
 - (1 x) 543 x 445 x 118 mm
 - (1 x) 543 x 445 x 184 mm



1475K8PC	0182923	2	677x501x965	1 100	543x445xh	45	50x125	80	
1475K8PCM	0182930	2	677x501x965	1 100	543x445xh	45	50x125	80	
1475K8PDG	0183302	2	677x501x965	1 100	543x445xh	45	50x125	80	
1475K8PEV	0182947	2	677x501x965	1 100	543x445xh	45	50x125	80	
1475K8PSP	0183357	2	677x501x965	1 100	543x445xh	45	50x125	80	
1475K8PJJ	0182961	2	677x501x965	1 100	543x445xh	45	50x125	80	
1475K8PAW	0182978	2	677x501x965	1 100	543x445xh	45	50x125	80	
1475K8PSV	0189962	1	677x501x965	1 100	543x445xh	45	50x125	80	